

# ACL-0040

ACL-0040

|                        |  |
|------------------------|--|
| Product Description#   | ChraLamp, Hollow-Cathode Lamp<br>ACL-0040  |
| Lifetime#              | 5000 mA/hrs  |
| Lamp Brand             | ChraLamp   |
| Window material#       | Synthetic quartz   |
| Instrument Used#       | Shimadzu AA  |
| OEM Part#              | -  |
| Alternative for#       | -  |
| Lamp Current#          | -  |
| ChraLamp Line ACL-0040 | Value Line   |
| ChraLamp URL           | <a href="https://chralamp.com">ACL-0040</a> at <a href="https://chralamp.com">https://chralamp.com</a> |
| ChraLamp Part#         | ACL-0040   |
| Lamp Type              | Hollow Cathode Lamp (HCL AA Is   |
| Product Type           | Laboratory Consumables and Eq  |
| Part Type              | Replacement/ alternative spare   |
| For Use with           | Laboratory Equipment (Atomic A   |
| Manufacturer           | Chratec  |
| AALamp URL             | <a href="https://aalamp.com">ACL-0040</a> at <a href="https://aalamp.com">https://aalamp.com</a>       |
| Installation           | Please see instrument manual fo  |

|             |  |
|-------------|--|
| Replacement | Beyond routine maintenance                                   |
| Warranty#   | See ChraContact at <a href="https://chrat">https://chrat</a> |

---

Revision #1

Created 4 August 2021 07:05:39 by Admin

Updated 4 August 2021 07:05:47 by Admin