

# ACL-1480

ACL-1480

|                        |  |
|------------------------|--|
| Product Description#   | ChraLamp, Hollow-Cathode Lamp 1480   |
| Lifetime#              | 5000 mA/hrs  |
| Lamp Brand             | ChraLamp   |
| Window material#       | Synthetic quartz   |
| Instrument Used#       | Varian AA  |
| OEM Part#              | -  |
| Alternative for#       | -  |
| Lamp Current#          | -  |
| ChraLamp Line ACL-1480 | Quality Line   |
| ChraLamp URL           | <a href="https://chralamp.com">ACL-1480</a> at <a href="https://chralamp.com">https://chralamp.com</a> |
| ChraLamp Part#         | ACL-1480   |
| Lamp Type              | Hollow Cathode Lamp (HCL AA Is   |
| Product Type           | Laboratory Consumables and Eq  |
| Part Type              | Replacement/ alternative spare   |
| For Use with           | Laboratory Equipment (Atomic A   |
| Manufacturer           | Chratec  |
| AA Lamp URL            | <a href="https://aalamp.com">ACL-1480</a> at <a href="https://aalamp.com">https://aalamp.com</a> ,     |
| Installation           | Please see instrument manual fo  |

|             |  |
|-------------|--|
| Replacement | Beyond routine maintenance   |
| Warranty#   | See ChraContact at <a href="https://chrata.com">https://chrata.com</a> |

---

Revision #1

Created 9 August 2021 03:50:31 by Admin

Updated 9 August 2021 03:50:40 by Admin